



EPOXY QUICK SET

CRYSTAL CLEAR FAST DUAL-COMPONENT EPOXY ADHESIVE



PRODUCT DESCRIPTION

Crystal clear fast dual-component epoxy adhesive

FIELD OF APPLICATION

Suitable for fast, strong and invisible repair of many materials, such as pottery, porcelain, glass, leather, wood, stone, metal, ceramics. Both with themselves and in combination.

Not suitable for Polyethylene (PE), polypropylene (PP), PTFE and silicone rubber.

PROPERTIES

- Fast
- Crystal clear
- Super-strong
- Universal, suitable for many materials
- Resistant to temperatures between -40°C and $+100^{\circ}\text{C}$
- Filling
- Water resistant
- Chemical resistant
- Paintable

PREPARATION

Working Conditions: Recommended application at temperatures between $+10^{\circ}\text{C}$ and $+35^{\circ}\text{C}$. Product cures by mixing the resin and hardener.

Personal safety: Preferably wear gloves.

Surface Requirements: The surface must be dry, clean and free of dust and grease.

Preliminary Surface Treatment: Degrease parts to be bonded with denatured alcohol. Roughen smooth surfaces (sandpaper).

Tools: Clean tools immediately after use with warm water and soap.

APPLICATION

Coverage: 1 ml = approx 10 cm² at a film thickness of 1 mm

Directions for use:

The surfaces to be bonded must be clean, dry and free from oil and grease. Smooth surfaces should be roughened. Break the nozzle and seal. Screw on enclosed mixer. Squeeze adhesive out of the syringe and apply to one side, to both sides with rough materials. Put parts together to fit exactly without pressure. Process time approximately 5 minutes at room temperature. The functional strength is reached after 20 min, final bonding strength after 12 h (both at room temperature). Unscrew and dispose mixer after use. Clean syringe nozzles and seal with cap. Use second mixer for next use. Store in upright position, in a cool, dry place. Do not use at temperatures below 10°C .

Stains/residue: Remove wet stains immediately with warm water and soap. Cured adhesive residue can only be removed mechanically.

Advice: Some types of synthetics can not be joined such as polyethylene and polypropylene. Use a piece of adhesive tape in order to keep the parts in place while the adhesive is curing.

Points of attention: After use close well (note: always place back the cap in the same way, due to the bonding of the cap to the double syringe). For optimum performance it is important to create a larger amount of adhesive and mix it very well. Curing time depends on the temperature. Adhesive does not cure below $+5^{\circ}\text{C}$.

Our advice is based on extensive research and practical experience. However, in view of the large variety of materials and the conditions under which our products are applied, we assume no responsibility for the results obtained and/or any damage caused by the use of the product. Nevertheless, our Service Department is always at your disposal for any advice needed.



EPOXY QUICK SET

CRYSTAL CLEAR FAST DUAL-COMPONENT EPOXY ADHESIVE

TECHNICAL SPECIFICATIONS

Bonding technique:	1-Sided application
Chemical base:	Epoxy resin
Chemicals resistance:	Water, oil, grease, solvents, diluted acids and alkalis
Colour:	Transparent
Colour after curing/drying:	Transparent
Consistency:	Liquid
Density approx.:	1,16 g/cm ³
Filling capacity:	Very good
Final bond strength (Alu):	17 N/mm ²
Final bond strength after:	12 hours
Handling time:	20 minutes
Minimum application temperature:	5 °C
Minimum temperature resistance:	-40 °C
Maximum temperature resistance:	100 °C
Moisture resistance:	Good
Mixture ratio:	1:1
Paintability:	Yes
Potlife:	5 minutes
Solvent free:	Yes
UV resistance:	Good
Viscosity:	Medium viscosity
Viscosity approx.:	20000 mPa·s
Water resistance:	Good
Water soluble:	No

STORAGE CONDITIONS

Store in tightly closed packaging in a dry, cool and frost-free place.

Our advice is based on extensive research and practical experience. However, in view of the large variety of materials and the conditions under which our products are applied, we assume no responsibility for the results obtained and/or any damage caused by the use of the product. Nevertheless, our Service Department is always at your disposal for any advice needed.